

Bảng thông số sản phẩm

Thông số kỹ thuật



contactor CT - 2 poles - 2 NO - 25 A
- 230..240 V AC

15959

⚠️ Ngày sản xuất vào: 23 thg 1, 2021

⚠️ Ngày sản xuất

Main

Product Or Component Type	Contactor
Device Short Name	CT
Device Application	Control circuit
Poles	2P
[Ie] Rated Operational Current	25 A AC-7A
Pole Contact Composition	2 NO
Network Type	AC
Control Type	Remote control
[Uc] Control Circuit Voltage	230/240 V AC 50 Hz

Complementary

Network Frequency	50 Hz
[Ue] Rated Operational Voltage	250 V AC 50 Hz
Maximum Power	3 W at 250 V AC
Control Signal Type	Maintained
Local Signalling	Color indicator
Hold-In Power Consumption In Va	2.7 VA
Inrush Power In Va	9.2 VA
Mounting Mode	Clip-on
Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	60 mm
Colour	Grey
Mechanical Durability	1000000 cycles
Electrical Durability	30000 cycles IEC/EN 61095 50 Hz AC-7C 30000 cycles EN/IEC 60947-4-1 50 Hz AC-3 30000 cycles EN/IEC 60947-4-1 50 Hz AC-5a

Connections - Terminals	Power circuit: tunnel type terminals2 cable(s) 2.5 mm² flexible Power circuit: tunnel type terminals1 cable(s) 6 mm² rigid Control circuit: tunnel type terminals2 cable(s) 2.5 mm² flexible Control circuit: tunnel type terminals2 cable(s) 1.5 mm² rigid
-------------------------	--

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Product Compatibility	Auxiliary contact Time delay Interference filter Mixed control: impulse/latched
Compatibility Code	CT

Environment

Standards	IEC/EN 61095
Product Certifications	IMQ VDE CEBEC CCC EAC
Noise Level	30 dB
Ip Degree Of Protection	IP20
Pollution Degree	2
Tropicalisation	2 conforming to EN 60947-4-1 2 conforming to EN 61095 2 conforming to IEC 1095
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-5...60 °C
Ambient Air Temperature For Storage	-40...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.118 kg

Contractual warranty

Warranty	18 months
----------	-----------