

Bảng thông số sản phẩm

Thông số kỹ thuật



C60 - circuit breaker - C60L - 4P - 16A - B curve

25385

⚠️ Ngày sản xuất vào: 27 thg 8, 2021

⚠️ Ngày sản xuất

Main

Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60L
Device Application	Distribution
Poles Description	4P
Number Of Protected Poles	4
[In] Rated Current	16 A at 40 °C
Network Type	DC AC
Trip Unit Technology	Thermal-magnetic
Curve Code	B
Breaking Capacity	20 kA Icu at 440 V AC 50/60 Hz conforming to EN/IEC 60947-2 50 kA Icu at 230...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 25 kA Icu at 400...415 V AC 50/60 Hz conforming to EN/IEC 60947-2 30 kA Icu at 125 V DC 2P conforming to EN/IEC 60947-2 50 kA Icu at 125 V DC 3P conforming to EN/IEC 60947-2 60 kA Icu at <= 250 V DC 4P conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	440 V AC 50/60 Hz 230...240 V AC 50/60 Hz 400...415 V AC 50/60 Hz <= 250 V DC
Magnetic Tripping Limit	3.2...4.8 x In
[Ics] Rated Service Breaking Capacity	10 kA conforming to EN/IEC 60947-2 - 440 V AC 50/60 Hz 25 kA conforming to EN/IEC 60947-2 - 230...240 V AC 50/60 Hz 12.5 kA conforming to EN/IEC 60947-2 - 400...415 V AC 50/60 Hz
Limitation Class	3 conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Clip-on

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	NO
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	73 mm
Net Weight	0.48 kg
Mechanical Durability	20000 cycles
Connections - Terminals	Tunnel type terminals16 mm² flexible Tunnel type terminals25 mm² rigid
Tightening Torque	Power circuit: 2 N.m upside 2 N.m downside
Earth-Leakage Protection	Separate block
Product Compatibility	C60 accessories C60 auxiliary

Environment

Standards	EN/IEC 60947-2 EN 60898
Tropicalisation	2 conforming to IEC 60068-1
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	7.2 cm
Package 1 Length	8.5 cm
Package 1 Weight	455.467 g

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)

Hiệu suất sức khỏe

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Plastic Parts & Cables Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins