

Bảng thông số sản phẩm

Đặc điểm

48725

circuit breaker Masterpact NW08H10 - 800 A - 3 poles - drawout



Main

Range of product	Masterpact NW
Product or component type	Basic frame
Device short name	Masterpact NW08 1000V
Circuit breaker name	Masterpact NW08HA10
Poles description	3P
Network type	AC
Breaking capacity code	H10
Suitability for isolation	Yes conforming to IEC 60947-2
Utilisation category	Category B

Complementary

Network frequency	50/60 Hz
Control type	Push-button
Mounting mode	Drawout
[In] rated current	800 A at 40 °C
[Ui] rated insulation voltage	1250 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	12 kV conforming to IEC 60947-2
[Icm] rated short-circuit making capacity	105 kA 1150 V AC at 50/60 Hz
[Ue] rated operational voltage	1150 V AC 50/60 Hz conforming to IEC 60947-2
Breaking capacity	50 kA Icu at 1150 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] rated service breaking capacity	50 kA at 1150 V AC 50/60 Hz conforming to IEC 60947-2
Protection type	Without protection
Mechanical durability	12500 cycles without maintenance conforming to IEC 60947-2 25000 cycles with maintenance conforming to IEC 60947-2
Electrical durability	500 cycles 1150 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
Connection pitch	115 mm

[Icw] rated short-time withstand current	50 kA 1 s conforming to IEC 60947-2 50 kA 3 s conforming to IEC 60947-2
Maximum breaking time	25 ms
Maximum closing response time	70 ms
Height	439 mm
Width	441 mm
Depth	394.5 mm

Environment

Standards	IEC 60947-2
Product certifications	ASEFA ASTA
Pollution degree	3 conforming to IEC 60664-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------