

Bảng thông số sản phẩm

Đặc điểm

AP9420

InfraStruXure® Manager Appliance, 25 Node



⚠ Ngừng sản xuất

Overview

Lead time While Supplies Last

General

Provided equipment Country-specific detachable power cord
Installation guide
Rack mounting brackets

Physical

Colour Black
Depth 17.15 cm
Height 4.45 cm
Mounting location Front
Net weight 3 kg
Width 43.18 cm

Conformance

Standards EN 55022 class A
EN 55024
EN 60950
EN 61000-3-2
FCC part 15 class A
ICES-003
UL 60950
Product certifications AS/NZS 3548 (C-Tick) class A
CUL listed
CE
UL listed
VDE

Environmental

Ambient air temperature for operation 5...40 °C

Operating altitude	0...10000 ft
Relative humidity	5...95 %
Ambient air temperature for storage	5...40 °C
Storage altitude	0.00...3048.00 m
Storage Relative Humidity	5...95 %

Packing Units

Package 1 Weight	5.23 kg
Package 1 Height	21.59 cm
Package 1 width	57.79 cm
Package 1 Length	33.66 cm

Contractual warranty

Warranty	2 year (manufacturer's defect)
----------	--------------------------------