

Bảng thông số sản phẩm

Thông số kỹ thuật



TeSys LG - enclosed DOL starter - 0.16...0.25 A - 220/230 V AC coil

LG1K065M702

Main

Range	TeSys
Product Name	TeSys LG
Device Short Name	LG1K
Product Or Component Type	Enclosed DOL starter
Device Application	Safety
Utilisation Category	AC-3
Device Composition	Contactor Switch disconnecter Circuit-breaker
Motor Power Kw	0.06 kW at 400/415 V AC 50/60 Hz 0.06 kW at 440 V AC 50/60 Hz
Thermal Protection Adjustment Range	0.16...0.25 A
[Uc] Control Circuit Voltage	220/230 V AC 50/60 Hz
Control Type	Push-button start white I Push-button stop black O Rotary handle emergency stop red

Complementary

Cable Entry Number	4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom
Width	175 mm
Height	165 mm
Depth	165 mm
Net Weight	0.97 kg

Environment

Standards	IEC 60947-4-1 IEC 60204-1
Material	Polycarbonate
Ik Degree Of Protection	IK07 conforming to IEC 60529
Ip Degree Of Protection	IP55 conforming to IEC 60529
Environmental Characteristic	Standard environment

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Number Of Units In Package 1	1
------------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------