

Bảng thông số sản phẩm

Thông số kỹ thuật



Linergy DS - screw distribution block 4P - 100A - 28 holes

LGY410028

⚠️ **Ngừng sản xuất vào:** 1 thg 11, 2020

⚠️ **Ngừng sản xuất**

Main

Range	Linergy
Product Name	Linergy DS
Product Or Component Type	Distribution block

Complementary

Mounting Support	DIN rail
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys ComPact
Product Compatibility	Spacial enclosures
Poles Description	4P
Distribution Block Outgoers	4 x 7 holes
[Ue] Rated Operational Voltage	230 V AC Ph/N 440 V AC Ph/Ph
[Ui] Rated Insulation Voltage	500 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ie] Rated Operational Current	100 A at 40 °C
[Icw] Rated Short-Time Withstand Current	3 kA for 1 s
[Ipk] Rated Peak Withstand Current	24 kA
Connections - Terminals	Supply: screw terminal 2 cable(s) 2.5...25 mm ² rigid Supply: screw terminal 2 cable(s) 1.5...16 mm ² flexible with cable end Distribution: screw terminal 5 cable(s) 1.5...16 mm ² rigid Distribution: screw terminal 5 cable(s) 1.5...10 mm ² flexible with cable end
Tightening Torque	Supply: 2 N.m flat screwdriver 7.5 mm Supply: 2 N.m PZ2 screwdriver 7.5 mm Distribution: 2 N.m flat screwdriver 5.5 mm Distribution: 2 N.m PZ2 screwdriver 5.5 mm
9 Mm Pitches	8
Height	100 mm
Width	71 mm
Depth	50.5 mm

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Net Weight	0.21 kg
Colour	White (RAL 9003)

Environment

Pollution Degree	3
Overvoltage Category	III
Dielectric Strength	2500 V
Standards	EN/IEC 61439-1 EN/IEC 60947-7-1
Ambient Air Temperature For Operation	-25...55 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.800 cm
Package 1 Width	10.500 cm
Package 1 Length	13.400 cm
Package 1 Weight	245.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	34
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.880 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	272
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	84.400 kg

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)

Hiệu suất sức khỏe

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins