

Bảng thông số sản phẩm

Thông số kỹ thuật



Thermal overload relay, TeSys Deca, 690VAC, 48 to 65A, 1NO+1NC, class 10A, EverLink BTR screw

LRD365

Main

Range	TeSys TeSys Deca
Product Name	TeSys LRD TeSys Deca
Product Or Component Type	Differential thermal overload relay
Device Short Name	LRD
Relay Application	Motor protection
Product Compatibility	LC1D65A LC1D50A
Network Type	DC AC
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Thermal Protection Adjustment Range	48...65 A
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1

Complementary

Network Frequency	0...400 Hz
Mounting Support	Plate, with specific accessories Rail, with specific accessories Under contactor
Tripping Threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for signalling circuit
Permissible Current	0.95 A at 380 V AC-15 for signalling circuit 0.06 A at 440 V DC-13 for signalling circuit
[Ue] Rated Operational Voltage	690 V AC 0...400 Hz for power circuit conforming to IEC 60947-4-1
Associated Fuse Rating	4 A gG for signalling circuit 4 A BS for signalling circuit
[Uimp] Rated Impulse Withstand Voltage	6 kV
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Control Type	Red push-button: stop Blue push-button: reset
Temperature Compensation	-20...60 °C

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Connections - Terminals	Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm² flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm² flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 1...2.5 mm² solid without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm² flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm² flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 1...35 mm² solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 5 N.m - on EverLink BTR screw connectors
Height	70 mm
Width	55 mm
Depth	123 mm
Net Weight	0.375 kg

Environment

Climatic Withstand	conforming to IACS E10
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-20...60 °C without derating conforming to IEC 60947-4-1
Ambient Air Temperature For Storage	-60...70 °C
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 4 gn conforming to IEC 60068-2-6
Dielectric Strength	1.89 kV at 50 Hz conforming to IEC 60947-1
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 GB/T 14048.4 GB/T 14048.5 EN 50495
Product Certifications	IEC UL CSA CCC EAC DNV-GL RMRS EU-RO MR LROS (Lloyds register of shipping) ATEX INERIS UKCA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.200 cm
Package 1 Width	11.000 cm
Package 1 Length	14.000 cm
Package 1 Weight	394.000 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	13
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.453 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	208
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	97.732 kg

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

✓ Reach Free Of Svhc	
✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information