

Bảng thông số sản phẩm

Thông số kỹ thuật



C60 - circuit breaker - C60N - 1P - 20A - C curve

MGN60869

⚠ **Ngừng sản xuất vào:** 23 thg 1, 2021

⚠ **Ngừng sản xuất**

Main

Range Of Product	C60
Range	Multi9
Product Name	C60
Product Or Component Type	Miniature circuit-breaker
Device Short Name	C60N
Device Application	Distribution
Poles Description	1P
Number Of Protected Poles	1
[In] Rated Current	20 A at 50 °C conforming to EN/IEC 60947-2
Network Type	DC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	10 kA Icu at 240 V AC 50/60 Hz phase to neutral conforming to EN/IEC 60947-2 3 kA Icu at 415 V AC 50/60 Hz phase to neutral conforming to EN/IEC 60947-2
Utilisation Category	Category A conforming to EN/IEC 60947-2
Suitability For Isolation	Yes conforming to EN/IEC 60947-2

Complementary

[Ue] Rated Operational Voltage	240 V AC 50/60 Hz phase to neutral
Magnetic Tripping Limit	8.5 x In +/- 20 %
[Ics] Rated Service Breaking Capacity	7.5 kA 75 % conforming to EN/IEC 60947-2 - 240 V AC 50/60 Hz 2.25 kA 75 % conforming to EN/IEC 60947-2 - 415 V AC 50/60 Hz
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Top or bottom: YES
9 Mm Pitches	2
Height	81 mm
Width	18 mm

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Depth	73 mm
Net Weight	0.12 kg
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles conforming to EN/IEC 60947-2
Connections - Terminals	Tunnel type terminals1...25 mm² rigid Tunnel type terminals1...25 mm² flexible without cable end Tunnel type terminals1...25 mm² flexible with cable end
Wire Stripping Length	Power circuit: 14 mm
Tightening Torque	Power circuit: 2 N.m
Earth-Leakage Protection	Separate block
Product Compatibility	C60 auxiliary C60 accessories

Environment

Standards	EN/IEC 60947-2
Product Certifications	RINA IACS E10 GL DNV RMRoS KRS LRS ABS BV
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-2
Pollution Degree	3 conforming to EN/IEC 60947-2
Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...80 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	1.8 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.106 kg

Contractual warranty

Warranty	18 months
----------	-----------