

Bảng thông số sản phẩm

Thông số kỹ thuật



ClimaSys CV - CSVS SmartFan 300m3/h 230V IP54

NSYCVF300M230DG

Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Range Compatibility	Spacial
Type Of Filter	G2
Flow Rate	Free flow rate with standard filter: 300 m3/h at 50 Hz Free flow rate with standard filter: 350 m3/h at 60 Hz
[Us] Rated Supply Voltage	145...253 V
Input Voltage	230 V 50/60 Hz
Certification	CE EAC EMC directive 89/336 EEC

Complementary

Absorbed Power	36 W 50 Hz 37 W 60 Hz
[In] Rated Current	0.16 A 50 Hz 0.17 A 60 Hz
Noise Level < At	55...56 dB
Bearing Type	Ball
Height	External: 268 mm
Width	External: 248 mm
Depth	External : 116 mm
Cut-Out Dimensions	223 x 223 mm
Net Weight	1.640 kg
Material	Outlet grille: injected thermoplastic (PC) Motor support: injected thermoplastic (ASA PC)
Colour	Outlet grille: smoked black (RAL 9005) Motor support: black (RAL 9005)
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Maximum Pressure	158 Pa flow rate 0 m³/h
Connections - Terminals	Faston connector

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Device Composition	1 axial motor 1 external protective transparent smoked grille: front 1 smart filter with dust sensor 1 fan sensor ready to be mounted: rear of outlet grille 1 cable gland 1 cut-out template
Condition Of Use	Filter must be cleaned and replaced regularly Flow rates depends on the work point, see ProClima software Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Outside temperature must be 5 °C lower than inside temperature

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.4 cm
Package 1 Width	24.8 cm
Package 1 Length	26.8 cm
Package 1 Weight	1.64 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	28.5 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.838 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe

 Mercury Free

 Rohs Exemption Information [Yes](#)

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information