

# Bảng thông số sản phẩm

Thông số kỹ thuật



## Spacial SD Compact control desk w/o mounting plate - H1000xW1000xD466 - IP55

NSYSD10

### Main

|                      |                                                                                                                 |
|----------------------|-----------------------------------------------------------------------------------------------------------------|
| Range                | Spacial                                                                                                         |
| Product Name         | Spacial SD                                                                                                      |
| Enclosure Type       | Multi-purpose                                                                                                   |
| Category             | Monobloc control desk                                                                                           |
| Nominal Height       | 1000 mm                                                                                                         |
| Nominal Width        | 1000 mm                                                                                                         |
| Nominal Depth        | 466 mm                                                                                                          |
| Product Installation | Floor-standing                                                                                                  |
| Device Composition   | 1 structure<br>2 lock: door<br>4 adjustment rail<br>1 cable gland plate<br>2 pneumatic stay: desk lid<br>2 door |

### Complementary

|                             |                                                                              |
|-----------------------------|------------------------------------------------------------------------------|
| Body Type                   | Single piece structure folded and welded                                     |
| Door Type                   | Plain                                                                        |
| Number Of Doors             | Front: 2 door(s)                                                             |
| Door Opening Side           | Reversible 120 ° door                                                        |
| Lock Type                   | 2 points lock, 3 mm double-bar                                               |
| Mounting Plate Description  | Without mounting plate                                                       |
| Type Of Gland Plate         | 1 entry plate                                                                |
| Accessibility For Operation | Front                                                                        |
| Removable Parts             | Door by hinges<br>Desk lid by hinges<br>Cable gland plate by clipping screws |
| Material                    | Body: steel                                                                  |
| Surface Finish              | Epoxy-polyester powder                                                       |
| Thickness                   | 1.5 mm                                                                       |

### Environment

|                         |                              |
|-------------------------|------------------------------|
| Standards               | IEC 62208                    |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Ik Degree Of Protection | IK10 conforming to IEC 62262 |

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 114.5 cm |
| Package 1 Width              | 101.5 cm |
| Package 1 Length             | 47.6 cm  |
| Package 1 Weight             | 60.0 kg  |
| Unit Type Of Package 2       | PAM      |
| Number Of Units In Package 2 | 2        |
| Package 2 Height             | 120 cm   |
| Package 2 Width              | 100 cm   |
| Package 2 Length             | 130 cm   |
| Package 2 Weight             | 149 kg   |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Bền vững



Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO<sub>2</sub> thấp.

**Hướng dẫn đánh giá tính bền vững của sản phẩm** là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch    RoHS/REACH

Hiệu suất sức khỏe

 Mercury Free

 Rohs Exemption Information    [Yes](#)

Chứng nhận & Tiêu chuẩn

|                          |                                                                                                                       |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Reach Regulation         | <a href="#">REACH Declaration</a>                                                                                     |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)                                                            |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>                                                                         |
| Circularity Profile      | No need of specific recycling operations                                                                              |