

Bảng thông số sản phẩm

Thông số kỹ thuật



Gas Insulated Switchgear, RM6,
NE-IDI, 20kA 1s, 630A, 24kV,
VIP400, non-extensible

RM6C1NEIDIR07

Main

Range Of Product	RM6
Product Or Component Type	Gas insulated switchboard
Device Application	Circuit breaker
Device Composition	Circuit-breaker 630 A
Enclosure Type	NE (not extensible)
Enclosure Name	IDI
Extensibility Kit	Not provided
Standards	IEC 62271-200
Network Type	AC
Rated Frequency (Fr)	50/60 Hz
Rated Voltage (Ur)	24 kV
Rated Continuous Current (Ir)	630 A
Rated Short-Time Withstand Current (Ik)	20 kA rms 1 s

Complementary

Pressure Sensor Type	Standard manometer, < 1000 m, temperature-25...40 °C
Ip Degree Of Protection	IP67
Function Available	3 functions
Bus Rated Current	630 A
User Manual	English
Ik Degree Of Protection	IK07
Relay Type	Current control relay VIP 400 CUAR
Local Signalling Voltage Indication	voltage presence indicator light with VPIS V2 sensor type
Interlocking Type	Without interlock
Height	1142 mm
Width	1186 mm
Depth	670 mm
Product Weight	240 kg

Environment

Ambient Air Temperature For Operation	-25...40 °C
---------------------------------------	-------------

Miễn trừ trách nhiệm: Tài liệu này không đảm bảo thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Operating Altitude	< 1000 m
--------------------	----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	116.0 cm
Package 1 Width	121.0 cm
Package 1 Length	71.0 cm
Package 1 Weight	260.0 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch RoHS/REACH

Hiệu suất sức khỏe



Rohs Exemption Information

Yes

Chứng nhận & Tiêu chuẩn

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information