

Bảng thông số sản phẩm

Thông số kỹ thuật



Monolithic precabled tower light,
Harmony XVC, plastic, red orange
green, 40mm, tube mounting,
steady, IP23, 24V AC DC

XVC4B3

Main

Range Of Product	Harmony XVC4
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	3 illuminated units
Sound Signalling	Without
Mounting Diameter	40 mm
Component Name	XVC
Device Short Name	XVC
Light Source	LED steady red LED steady orange LED steady green
Supply Circuit Type	AC/DC

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover SGP (chromium-plated): support tube
Mounting Location	On support tube, 17 mm
Product Mounting	On support tube, 17 mm
[Us] Rated Supply Voltage	24 V
[Us] Rated Supply Voltage	24 V
Cable Cross Section	0.33 mm ²
Awg Gauge	AWG 22
Cable Length	600 mm
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	75 mA
Flashing Frequency	1 Hz
Net Weight	0.54 kg
Height	473.5 mm

Environment

Standards	EN/IEC 61000-6-3 EN/IEC 61000-6-2
-----------	--------------------------------------

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-35...70 °C
Ambient Air Temperature For Operation	-10...50 °C
Electrical Shock Protection Class	Class I conforming to EN/IEC 61140
Overvoltage Category	Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP23 vertical surface installation conforming to EN/IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.800 cm
Package 1 Width	6.800 cm
Package 1 Length	75.200 cm
Package 1 Weight	758.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	17.500 cm
Package 2 Width	37.000 cm
Package 2 Length	77.500 cm
Package 2 Weight	8.684 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	20
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	25.368 kg

Contractual warranty

Warranty	18 months
----------	-----------

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch

Hiệu suất sức khỏe

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive [Pro-active compliance \(Product out of EU RoHS legal scope\)](#)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

Bảng thông số sản phẩm


XVC4B3

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



No. of illuminated units	b Without buzzer (mm)	b Without buzzer (in.)
1 stage	403.50	15.89
2 stages	438.50	17.26
3 stages	473.50	18.64
4 stages	508.50	20.02
5 stages	543.50	21.40

XVC4B3

Pre-assembled and Pre-wired Tower Light