Bảng thông số sản phẩm

Thông số kỹ thuật

Monolithic precabled tower light, Harmony XVC, plastic, red orange green, 60mm, tube mounting, steady, IP23, 24V AC DC

XVC6B3

Main

Range Of Product	Harmony XVC6
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	3 illuminated units
Sound Signalling	Without
Mounting Diameter	60 mm
Component Name	XVC
Light Source	LED steady red LED steady orange LED steady green
[Us] Rated Supply Voltage	24 V
Supply Circuit Type	AC/DC

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover STK (chromium-plated): support tube
Product Mounting	On support tube, 22 mm
Cable Cross Section	0.33 mm²
Awg Gauge	AWG 22
Cable Length	600 mm
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	75 mA
Flashing Frequency	1 Hz
Net Weight	0.78 kg
Height	508.3 mm

Environment

Standards	IEC 61000-6-4 IEC 61000-6-2 IEC 61000-6-3
Product Certifications	UL
Protective Treatment	TC
Ambient Air Temperature For Storage	-35…70 °C

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Ambient Air Temperature For Operation	-10…50 °C
Electrical Shock Protection Class	Class I conforming to IEC 61140
Ip Degree Of Protection	IP23 vertical surface installation conforming to IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	78.000 cm
Package 1 Length	9.000 cm
Package 1 Weight	1.045 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	21.000 cm
Package 2 Width	46.000 cm
Package 2 Length	79.000 cm
Package 2 Weight	10.450 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	20
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	29.400 kg

Contractual warranty

Warranty	18 months

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO_2 thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

Tìm hiểu thêm về Green Premium >

Hướng dẫn đánh giá về sự bền vững của sản phẩm >

Minh bạch

Hiệu suất sức khoẻ

Mercury Free	
Rohs Exemption Information	Yes

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Bảng thông số sản phẩm

XVC6B3

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



No. of illuminated units	b Without buzzer (mm)	b Without buzzer (in.)
1 stage	428.3	16.86
2 stages	468.3	18.44
3 stages	508.3	20.01
4 stages	548.3	20.01
5 stages	588.3	23.16

Mounting and Clearance

Pre-assembled and Pre-wired Tower Light

Support Tube Mounting