

Bảng thông số sản phẩm

Thông số kỹ thuật



Remote control, Harmony eXLhoist, standard, display, 6 motion push buttons, 6 auxiliary push buttons

ZART12D

⚠ Ngừng sản xuất vào: 1 thg 11, 2020

⚠ Ngừng sản xuất

Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Hand-held remote control
Device Short Name	ZART
Control Button Type	6 configurable motion push-button 6 configurable auxiliary push-button

Complementary

Material	Enclosure: PC (polycarbonate) Enclosure: PBT (polybutylene terephthalate) Cover: PP (polypropylene) Protective cover: EPDM rubber
Function Available	Accelerometer function Vibrator function
Display Type	LCD display 34 x 42 mm
Operating Distance	50 m
Mechanical Robustness	Free fall resistance 4.5 m conforming to IEC 60068-2-27
Communication Network Type	Wireless: bluetooth low energy
Transmission Frequency	2.4 GHz
Maximum Sensing Distance	100 m in free field
Response Time	< 300 ms at full duplex
Charging Time	900 s
Autonomy	30 h
Mechanical Durability	5000000 cycles
Service Life	5 year(s)
Width	100 mm
Height	340 mm
Depth	90 mm
Net Weight	0.65 kg

Environment

Miễn trừ trách nhiệm: Tài liệu này không nhằm thay thế và không được sử dụng để xác định tính phù hợp hoặc độ tin cậy của các sản phẩm này cho các ứng dụng người dùng cụ thể

Radio Agreement	FCC ARIB RSS ICASA ANATEL SRRC
Ip Degree Of Protection	IP65
Nema Degree Of Protection	NEMA 4
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...45 °C
Operating Altitude	0...2000 m
Storage Altitude	0...3000 m
Vibration Resistance	0.075 mm conforming to IEC 60068-2-6 (f = 10...55 Hz)
Shock Resistance	100 gn conforming to IEC 60068-2-27
Relative Humidity	0...95 % at -20...60 °C operating
Product Certifications	C-Tick CSA CE JIS KC EAC UL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.700 cm
Package 1 Width	10.200 cm
Package 1 Length	33.700 cm
Package 1 Weight	749.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.485 kg

Bền vững

Nhãn **Green Premium™** là cam kết của Schneider Electric trong việc cung cấp sản phẩm với hiệu suất môi trường tốt nhất. Green Premium cam kết tuân thủ các quy định mới nhất, minh bạch về tác động môi trường, cũng như các sản phẩm tuần hoàn và CO₂ thấp.

Hướng dẫn đánh giá tính bền vững của sản phẩm là tài liệu kỹ thuật phổ thông giúp làm rõ các tiêu chuẩn nhãn sinh thái toàn cầu và cách diễn giải việc khai báo môi trường.

[Tìm hiểu thêm về Green Premium >](#)

[Hướng dẫn đánh giá về sự bền vững của sản phẩm >](#)



Minh bạch

Hiệu suất sức khỏe



Mercury Free



Rohs Exemption Information

[Yes](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)

Dimensions

