

In pursuance of a malfunctioning experienced by a financial intermediary in charge of bearer shares custody, the voting results of the Annual General Meeting of April 23, 2020 have to be corrected. The corrections are minor (in a range of -0,82% to +0,63%) and are without any consequence, neither on the quorum nor on the approval of the resolutions: all the 2020 resolutions remain validly approved. The corrected voting results are presented hereunder.

Number of shares constituting the share capital: 582,068,555

Number of shares having a right to vote: 554,301,302

	Ordinary						Extraordinary						
	Number		Shares		Voting rights		Number		Shares		Voting rights		
	Announced	Corrected	Announced	Corrected	Announced	Corrected	Announced	Corrected	Announced	Corrected	Announced	Corrected	
Shareholders attending the Combined General Meeting	-	-	-	-	-	-	-	-	-	-	-	-	
Proxy to the Chairman	1 769	1 769	1 320 287	1 320 287	2 001 745	2 001 745	1 759	1 759	1 312 149	1 312 149	1 987 973	1 987 973	
Proxy to another shareholder	-	-	-	-	-	-	-	-	-	-	-	-	
Vote by post	2 756	3 248	366 683 948	386 161 902	384 338 157	402 495 823	2 754	3 246	366 674 535	384 832 201	384 320 429	402 478 095	
Total	4 525	5 017	368 004 235	387 482 189	386 339 902	404 497 568	4 513	5 005	367 986 683	386 144 350	386 308 402	404 466 068	
Quorum	Announced	Corrected					Quorum	Announced	Corrected				
	66,39%	69,67%						66,38%	69,67%				

Resolutions	Type	Results announced on April 23, 2020				Corrected results				Difference
		For	Against	Abstention	Total For (en %)	For	Against	Abstention	Total For (en %)	
1	ord.	385 913 670	15 967	408 265	100,00%	404 071 336	15 967	408 265	100,00%	0,00%
2	ord.	385 912 569	16 924	408 409	100,00%	404 070 235	16 924	408 409	100,00%	0,00%
3	ord.	382 082 186	4 072 488	183 228	98,95%	398 170 090	6 142 250	183 228	98,48%	-0,47%
4	ord.	384 530 376	1 704 162	105 364	99,56%	402 688 042	1 704 162	105 364	99,58%	0,02%
5	ord.	375 033 191	11 024 365	195 950	97,14%	392 986 804	11 228 418	195 950	97,22%	0,08%
6	ord.	360 532 025	25 658 716	149 161	93,36%	376 218 874	28 129 533	149 161	93,04%	-0,32%
7	ord.	345 215 737	40 970 314	153 851	89,39%	360 829 864	43 513 853	153 851	89,24%	-0,15%
8	ord.	358 585 837	27 584 854	169 211	92,86%	376 269 726	28 058 631	169 211	93,06%	0,20%
9	ord.	341 641 129	35 652 390	9 046 383	90,55%	356 350 614	38 958 622	9 188 332	90,14%	-0,41%
10	ord.	363 325 363	22 858 303	156 236	94,08%	381 409 817	22 931 515	156 236	94,33%	0,25%
11	ord.	373 681 235	12 507 052	151 615	96,76%	390 122 428	14 223 525	151 615	96,48%	-0,28%
12	ord.	360 498 620	22 531 923	3 307 359	94,12%	377 450 476	23 725 655	3 319 437	94,09%	-0,03%
13	ord.	303 585 774	80 290 103	2 462 025	79,08%	320 471 002	81 550 463	2 474 103	79,71%	0,63%
14	ord.	379 677 733	6 454 855	205 314	98,33%	397 582 333	6 707 921	205 314	98,34%	0,01%
15	ord.	324 862 503	60 571 731	903 668	84,28%	341 324 834	62 267 066	903 668	84,57%	0,29%
16	ord.	333 405 623	52 830 815	101 464	86,32%	349 397 190	54 800 361	298 017	86,44%	0,12%
17	ord.	380 630 094	5 343 492	366 216	98,62%	398 703 919	5 427 333	366 216	98,66%	0,04%
18	extr.	381 994 208	4 211 499	100 695	98,91%	400 017 414	4 345 959	100 695	98,93%	0,02%
19	extr.	382 009 429	4 206 305	90 668	98,91%	400 032 635	4 340 765	90 668	98,93%	0,02%
20	extr.	374 220 542	12 029 505	58 355	96,89%	388 506 729	15 900 984	58 355	96,07%	-0,82%
21	extr.	374 740 991	11 506 883	60 528	97,02%	389 027 178	15 378 362	60 528	96,20%	-0,82%
22	ord.	386 242 350	4 417	91 135	100,00%	404 400 016	4 417	91 135	100,00%	0,00%

Exclusion of voting rights:

5th resolution: Emmanuel Babeau