

Product data sheet

Specifications



Mini Pragma L surface enclosure - IP30 - 1 x 12 modules - reversible front cover

10666

⚠ Discontinued on: Jun 26, 2020

⚠ Discontinued

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Distribution enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	1
Provided Equipment	1 marking kit 1 insulating plug
Type Of Door	Reversible
Width	283 mm
Height	185 mm
Depth	94 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Total Number Of 18 Mm Modules	13
Type Of Rail	DIN
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	IEC 60439-3 IEC 60695-2-1 EN 50102 IEC 60529 EN 60439-3 IEC 23-48
Fire Resistance	650 °C (30 s) conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications