

Product data sheet

Specifications



Kaedra - versatile - 448 x 842 mm - 17 pre-cutouts

13174

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

Range	Kaedra
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Versatile enclosure
Mounting Plate Description	Slotted

Complementary

Enclosure Mounting	Surface
Electrical Insulation Class	Double insulation Class II
Type Of Front Cover	Reversible Opaque
[In] Rated Current	160 A
Number Of Pre-Cutouts Pg Iso	17
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	842 mm
Depth	160 mm
Internal Depth	91 mm
Colour	Enclosure: light grey (RAL 7035)

Environment

Standards	EN 50262 IEC 670 IEC 60439-3 EN 50102 IEC 60529
Fire Resistance	750 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	85.200 cm
Package 1 Width	46.800 cm
Package 1 Length	16.800 cm
Package 1 Weight	7.378 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	11
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	92.000 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information