

Product data sheet

Specifications



Enclosure for power outlet, Mureva Enclosure, 1x12 modules, 6 openings 90x100mm, (W)340mm x (H)460mm, without term block

13181

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for power outlet
Mounting Plate Description	Without mounting plate

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	24
Number Of 18 Mm Modules Per Row	12
Total Number Of 18 Mm Modules	12
Number Of Horizontal Rows	1
Electrical Insulation Class	Class II Double insulation
Number Of Openings Of Interface	6
Number Of Plates	2 for push-button controls 6 for 65 x 85 power outlets
Provided Equipment	2 wiring strap 6 plate for 65 x 85 power outlet 2 plate for push-button control
Type Of Front Cover	Transparent
Power Dissipation In W	28 W
[In] Rated Current	63 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Locking Options Description	Optional keylock
Enclosure Material	Housing: self-extinguishing polymer
Net Weight	2.5 kg
Base Dimension	90 x 100 mm
Width	340 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Door: transparent green Enclosure: light grey (RAL 7035)
--------	---

Environment

Standards	IEC 61439-3 IEC 60695-2-1 IEC 60670 EN 62262 EN 50262
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.8 cm
Package 1 Width	36.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	2.848 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	28
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	91.744 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Lower Impact Materials Transparency RoHS/REACH

Resource performance

✓ Minimum Percentage Of Recycled Plastic Content 25

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Product

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations