

Product data sheet

Specifications



Polyvalent enclosure for power outlet, Mureva Enclosure, 1x18 modules, (W)448mm x (H)460mm, without terminal block

13193

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Versatile enclosure for power outlet
Mounting Plate Description	Slotted

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	18
Number Of Horizontal Rows	1
Electrical Insulation Class	Double insulation Class II
Type Of Front Cover	Transparent
Power Dissipation In W	39 W
[In] Rated Current	90 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Locking Options Description	Optional keylock
Enclosure Material	Housing: self-extinguishing polymer
Net Weight	3.4 kg
Width	448 mm
Height	460 mm
Depth	160 mm
Internal Depth	91 mm
Colour	Door: transparent green Enclosure: light grey (RAL 7035)

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60695-2-1 EN 50262 IEC 61439-3 EN 62262 IEC 60670
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	47.0 cm
Package 1 Length	47.0 cm
Package 1 Weight	3.741 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	18
Package 2 Height	115.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	79.338 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Lower Impact Materials Transparency RoHS/REACH

Resource performance

 Minimum Percentage Of Recycled Plastic Content 27

Well-being performance

 Rohs Exemption Information Yes

 Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations