

# Product data sheet

Specifications



## Mini Pragma surface enclosure - IP 40 - 1 x 6 modules - transparent door

13367

⚠ Discontinued on: Mar 31, 2022

⚠ Discontinued

### Main

|                             |                                                                                                           |
|-----------------------------|-----------------------------------------------------------------------------------------------------------|
| Range                       | Mini Pragma                                                                                               |
| Product Or Component Type   | Enclosure                                                                                                 |
| Enclosure Type              | Modular enclosure                                                                                         |
| Nb Of 18 Mm Modules Per Row | 6                                                                                                         |
| Nb Of Horizontal Rows       | 1                                                                                                         |
| Provided Equipment          | 1 marking kit<br>1 insulating plug<br>2 terminal block support<br>2 earth-neutral terminal blocks 4 holes |
| Type Of Door                | Transparent                                                                                               |
| Width                       | 148 mm                                                                                                    |
| Height                      | 200 mm                                                                                                    |
| Depth                       | 94 mm                                                                                                     |

### Complementary

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Enclosure Mounting            | Surface                                                                                  |
| 9 Mm Pitches                  | 12                                                                                       |
| Total Number Of 18 Mm Modules | 6                                                                                        |
| [In] Rated Current            | 63 A                                                                                     |
| [Ui] Rated Insulation Voltage | 690 V                                                                                    |
| Type Of Rail                  | DIN                                                                                      |
| Number Of Terminal Blocks     | 2 neutral / earth (Quick) with 4 outgoers                                                |
| Distribution Block Outgoers   | 4 x 10 mm <sup>2</sup> for earth / neutral<br>4 x 16 mm <sup>2</sup> for earth / neutral |
| Locking Options Description   | Keylock option                                                                           |
| Enclosure Material            | Enclosure: self-extinguishing material                                                   |
| Colour                        | Enclosure: white (RAL 9003)                                                              |

### Environment

|           |                                                                     |
|-----------|---------------------------------------------------------------------|
| Standards | EN 50102<br>IEC 60439-3<br>IEC 60529<br>EN 60439-3<br>IEC 60695-2-1 |
|-----------|---------------------------------------------------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                         |                                                                                                 |
|-------------------------|-------------------------------------------------------------------------------------------------|
| Fire Resistance         | Back part: 650 °C conforming to IEC 60695-2-1<br>Front face: 650 °C conforming to IEC 60695-2-1 |
| Ik Degree Of Protection | IK07 conforming to EN 50102                                                                     |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 9 cm     |
| Package 1 Width              | 14.7 cm  |
| Package 1 Length             | 20 cm    |
| Package 1 Weight             | 0.495 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|