

Product data sheet

Specifications



Mini Pragma surface enclosure - IP 40 - 1 x 8 modules - transparent door

13640

 **Discontinued on:** Mar 31, 2022

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Type Of Door	Transparent
Width	184 mm
Height	200 mm
Depth	94 mm

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
[In] Rated Current	63 A
Number Of Terminal Blocks	1 with 8 outgoers
Colour	Enclosure: white (RAL 9003)

Environment

Fire Resistance	Back part: 750 °C conforming to IEC 60695-2-1 Front face: 750 °C conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.5 cm
Package 1 Width	20 cm
Package 1 Length	9.5 cm
Package 1 Weight	0.52 kg

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months