

Product data sheet

Specifications



Mini Pragma flush enclosure - IP 40 - 3 x 12 modules - opaque door

13933

 **Discontinued on:** May 27, 2019

 **Discontinued**

Main

Range	Mini Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	12
Nb Of Horizontal Rows	3
Provided Equipment	1 marking kit 2 terminal block support 2 earth-neutral terminal blocks 22 holes
Type Of Door	Opaque

Complementary

Enclosure Mounting	Flush
9 Mm Pitches	24
Total Number Of 18 Mm Modules	36
[In] Rated Current	63 A
[Ui] Rated Insulation Voltage	690 V
Type Of Rail	DIN
Number Of Terminal Blocks	2 neutral / earth (Quick) with 22 outgoers
Distribution Block Outgoers	22 x 10 mm² for earth / neutral 22 x 16 mm² for earth / neutral
Locking Options Description	Keylock option
Enclosure Material	Enclosure: self-extinguishing material
Colour	Enclosure: white (RAL 9003)

Environment

Standards	EN 60439-3 IEC 60439-3 IEC 60695-2-1 EN 50102 IEC 60529
Fire Resistance	Back part: 650 °C conforming to IEC 60695-2-1 Front face: 650 °C conforming to IEC 60695-2-1
Ik Degree Of Protection	IK07 conforming to EN 50102

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	30 cm
Package 1 Length	47 cm
Package 1 Weight	1.87 kg

Contractual warranty

Warranty	18 months
----------	-----------