

Product data sheet

Specifications



Enclosure for modular device,
Mureva Enclosure, 3x18 modules,
earth terminal blocks

13986

Main

Range	Mureva
Product Name	Mureva Enclosure
Product Or Component Type	Weatherproof enclosure
Enclosure Type	Enclosure for modular device
Mounting Plate Description	Slotted

Complementary

Enclosure Mounting	Surface
9 Mm Pitches	36
Number Of 18 Mm Modules Per Row	18
Total Number Of 18 Mm Modules	54
Number Of Horizontal Rows	3
Electrical Insulation Class	Double insulation Class II
Provided Equipment	3 marking kit 3 wiring strap 1 terminal block 16 holes 1 terminal block 32 holes 2 terminal block support
Type Of Front Cover	Reversible Transparent
Power Dissipation In W	65 W
[In] Rated Current	125 A
Type Of Rail	DIN
Number Of Pre-Cutouts Pg Iso	17
Number Of Terminal Blocks	1 earth (screw connection) with 16 outgoing 1 earth (screw connection) with 32 outgoing
Distribution Block Outgoers	16 x 16 mm² + 16 x 10 mm² 8 x 16 mm² + 8 x 10 mm²
Locking Options Description	Optional keylock
Enclosure Material	Self-extinguishing polymer
Width	448 mm
Height	610 mm
Depth	160 mm
Internal Depth	88 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Door: transparent green Enclosure: light grey (RAL 7035)
--------	---

Environment

Standards	IEC 60670 EN 50262 IEC 60695-2-1 IEC 61439-3
Fire Resistance	650 °C conforming to IEC 60695-2-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 50102
Environmental Characteristics (Uv)	UV resistant: class 3 conforming to ISO 4582:2010 Ultraviolet degradation test conforming to ISO 4892-2:2013
Overvoltage Category	II
Ambient Air Temperature For Operation	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.000 cm
Package 1 Width	46.500 cm
Package 1 Length	62.000 cm
Package 1 Weight	5.705 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	19
Package 2 Height	80.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	120.395 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)




Lower Impact Materials Transparency RoHS/REACH

Resource performance

 Minimum Percentage Of Recycled Plastic Content 25

Well-being performance

 Rohs Exemption Information [Yes](#)

 Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations