

Product data sheet

Specifications



modular pilot light V - integral LED - yellow - 12..48 V

18334

⚠ Discontinued on: Apr 5, 2019

⚠ Discontinued

Main

Product Or Component Type	Modular pilot ligh
Device Short Name	V
[Us] Rated Supply Voltage	12...48 V AC at 50/60 Hz 12...48 V DC

Complementary

Indicator Light	LED yellow, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting Mode	Fixed
Mounting Support	Symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Auxiliary Connection Terminal	Tunnel type terminal 2 cable(s) flexible 2.5 mm² with cable end Tunnel type terminal 2 cable(s) flexible 2.5 mm² without cable end Tunnel type terminal 2 cable(s) rigid 2.5 mm² with cable end Tunnel type terminal 2 cable(s) rigid 2.5 mm² without cable end

Environment

Standards	IEC 60947-5-1
Ip Degree Of Protection	IP2 IPxx B
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...100 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	1.8 cm
Package 1 Length	7 cm
Package 1 Weight	0.04 kg

Contractual warranty

Warranty	18 months
----------	-----------