

Product data sheet

Specifications



Thorsman - nail clip - TC 3...5 mm - 1.2/20/15 - grey - set of 100

2011021

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

Main

Range	Thorsman
Range Of Product	Thorsman
Product Or Component Type	Nail clip
Device Short Name	TC
Device Application	Installation of round cable
Cable Type	Round cable 3...5 mm
Type Of Installation	Indoor
Provided Equipment	Nail
Nail Diameter	1.2 mm
Length	20 mm
Embedding Depth	15 mm

Complementary

Colour Tint	Grey (NCS 5402-Y)
Material	Clip: PP (polypropylene) Nail: electroplated hardened steel
Ambient Air Temperature For Operation	-40...80 °C

Environment

Environmental Characteristic	Impact resistant UV resistant
Quantity Per Set	Set of 100
Net Weight	0.00029 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.5 cm
Package 1 Width	0.7 cm
Package 1 Length	1.9 cm
Package 1 Weight	0.3 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	100
Package 2 Height	3.2 cm
Package 2 Width	5.0 cm
Package 2 Length	7.8 cm
Package 2 Weight	38.0 g
Unit Type Of Package 3	SFP
Number Of Units In Package 3	1000
Package 3 Height	7.8 cm
Package 3 Width	10.0 cm
Package 3 Length	17.4 cm
Package 3 Weight	366.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations