

# Product data sheet

Specifications



switch disconnecter, Compact  
INS63 , 63 A, standard version with  
black rotary handle, 4 poles

28903

## Main

Range	ComPact
Product name	Compact INS
Product or component type	Switch disconnecter
Poles description	4P
Network type	DC AC
Network frequency	50/60 Hz
[Ie] rated operational current	AC-22A: 63 A AC 50/60 Hz 220/240 V AC-22A: 63 A AC 50/60 Hz 380/415 V AC-22A: 63 A AC 50/60 Hz 440/480 V AC-22A: 63 A AC 50/60 Hz 500 V AC-23A: 40 A AC 50/60 Hz 500 V AC-23A: 63 A AC 50/60 Hz 220/240 V AC-23A: 63 A AC 50/60 Hz 380/415 V AC-23A: 63 A AC 50/60 Hz 440/480 V DC-22A: 63 A DC 125 V 2 poles in series DC-23A: 63 A DC 125 V 2 poles in series DC-22A: 63 A DC 250 V 4 poles in series DC-23A: 63 A DC 250 V 4 poles in series
[Ui] rated insulation voltage	690 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	8 kV
[Ith] conventional free air thermal current	63 A at 60 °C
[Icm] rated short-circuit making capacity	15 kA switch-disconnector alone 500 V AC at 50/60 Hz 75 kA with upstream protection circuit breaker 500 V AC at 50/60 Hz
[Ue] rated operational voltage	500 V AC 50/60 Hz 250 V DC
Suitability for isolation	Yes
Contact position indicator	Yes
Visible break	No
Pollution degree	3

## Complementary

Control type	Rotary handle
Handle colour	Black
Mounting mode	Fixed
Mounting support	Plate

	DIN rail
<b>Upside connection</b>	Front
<b>Downside connection</b>	Front
<b>Cable cross section</b>	1.5...50 mm <sup>2</sup>
<b>Maximum power</b>	AC-23: 15 kW at 220/240 V AC 50/60 Hz AC-23: 22 kW at 500/525 V AC 50/60 Hz AC-23: 30 kW at 380/415 V AC 50/60 Hz AC-23: 30 kW at 440 V AC 50/60 Hz
<b>Rated duty</b>	Uninterrupted
<b>Intermittent duty class</b>	Class 120 - 60 %
<b>Enclosure dimensions for lthe</b>	190 mm x 115 mm x 55 mm
<b>[l<sub>cw</sub>] rated short-time withstand current</b>	0.67 kA during 20 s conforming to IEC 60947-3 1.73 kA during 3 s conforming to IEC 60947-3 3 kA during 1 s conforming to IEC 60947-3 0.55 kA during 30 s conforming to IEC 60947-3
<b>Mechanical durability</b>	20000 cycles
<b>Electrical durability</b>	AC-22A: 1500 cycles 220/240 V AC 50/60 Hz AC-22A: 1500 cycles 380/415 V AC 50/60 Hz AC-22A: 1500 cycles 440 V AC 50/60 Hz AC-22A: 1500 cycles 500 V AC 50/60 Hz AC-23A: 1500 cycles 220/240 V AC 50/60 Hz AC-23A: 1500 cycles 380/415 V AC 50/60 Hz AC-23A: 1500 cycles 440 V AC 50/60 Hz AC-23A: 1500 cycles 500 V AC 50/60 Hz DC-22A: 1500 cycles 250 V DC 4 poles in series DC-23A: 1500 cycles 250 V DC 4 poles in series
<b>Connection pitch</b>	18 mm
<b>Height</b>	85 mm
<b>Width</b>	90 mm
<b>Depth</b>	62.5 mm
<b>Net weight</b>	0.6 kg

## Environment

<b>Standards</b>	IEC 60947-3 IEC 60947-1
<b>Product certifications</b>	CCC KEMA-KEUR
<b>IP degree of protection</b>	IP40 conforming to IEC 60529
<b>IK degree of protection</b>	IK07 conforming to EN 50102
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Ambient air temperature for storage</b>	-50...85 °C

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Weight</b>	650.0 g
<b>Package 1 Height</b>	10 cm
<b>Package 1 width</b>	9.2 cm
<b>Package 1 Length</b>	10 cm
<b>Unit Type of Package 2</b>	P12
<b>Number of Units in Package 2</b>	144
<b>Package 2 Weight</b>	109.784 kg

Package 2 Height	50 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	S03
Number of Units in Package 3	18
Package 3 Weight	12.064 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

## Contractual warranty

Warranty	18 months
----------	-----------