

Product data sheet

Specifications

Thorsman - TGS 3.5x32 - screw - panhead - set of 100



3709815

Main

Range Of Product	Thorsman
Product Or Component Type	Universal screw
Device Short Name	TGS
Device Application	Wood fibreboard and plasterboard Plug
Screw Type	Fully threaded with twin thread
Tool Type	power screwdriver cross-point
Quantity Per Set	Set of 100

Complementary

Screw Diameter	3.5 mm
Screw Length	32 mm
Shape Of Screw Head	Panhead
Screwdriver Shape	Philips No 2
Material	Screw: hardened steel electroplated

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.700 cm
Package 1 Width	0.700 cm
Package 1 Length	3.500 cm
Package 1 Weight	1.800 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations