

Product data sheet

Specifications



Performa - vertical/suspended/floor bracket - pre-galvanized - 185 mm

4551310

Main

Range of product	Performa
Product or component type	Vertical/suspended/floor bracket
Quantity per set	Set of 10

Complementary

Permanent permissible load	51 kg
Load bearing capacity	510 N
Product destination	Mesh tray
Mounting support	Threaded rod Wall Floor
Material	Sheet steel (pre-galvanized)
Height	38 mm
Width	185 mm
Depth	50 mm
Height compatibility	70 mm 35 mm
Width compatibility	100 mm
Surface treatment compatibility	Bi-chromated Electro-zinc
Market segment	Small commercial

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	242 g
Package 1 Height	3.8 cm
Package 1 width	5 cm
Package 1 Length	18.5 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	2.42 kg

Package 2 Height	5 cm
Package 2 width	21 cm
Package 2 Length	23 cm
Unit Type of Package 3	S03
Number of Units in Package 3	50
Package 3 Weight	12.1 kg
Package 3 Height	30 cm
Package 3 width	30 cm
Package 3 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------