

Product data sheet

Specifications



Vertical rear connection replacement kit, MasterPact NW40, 4 poles, fixed/drawout, 4000A, spare part

47969

Main

Range Of Product	MasterPact NW
Product Or Component Type	Rear connection
Accessory / Separate Part Category	Connection accessory
Range Compatibility	Masterpact MasterPact NW40
Poles Description	4P
Mounting Mode	Fixed + drawout
[In] Rated Current	4000 A

Complementary

Location Of Connection	Rear
Connection Position	Vertical
Connection Pitch	115 mm
Quantity Per Set	4
Accessory / Separate Part Category	Spare part

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.8 cm
Package 1 Width	13.0 cm
Package 1 Length	18.0 cm
Package 1 Weight	4.777 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	19.595 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)