

Product data sheet

Specifications



automatic insulation fault location XD308C Vigilohm - 220..240 V AC 50/60 Hz

50724

⚠ Discontinued - Service only

⚠ Discontinued on: Jul 21, 2023

⚠ To be end-of-service on: Dec 31, 2026

Main

Range	Vigilohm
Product Name	Vigilohm IFL
Device Short Name	XD308C
Number Of Channels	8
Mounting Position	Vertical

Complementary

Signalling Function	Insulation fault
Polling Time	20 s per connected channel
Test Function	Local
[Us] Rated Supply Voltage	220/240 V AC 50/60 Hz tolerance: - 15...10 %
Power Consumption In Va	6 VA
Mounting Mode	Flush-mounted
Mounting Support	Front face
Height	129 mm
Width	76 mm
Depth	115.5 mm
Net Weight	0.6 kg
Auxiliary Connection Terminal	Tunnel type terminals 1.5 mm²

Environment

Dielectric Strength	2500 V
Ip Degree Of Protection	IP30
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-25...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	13.5 cm
Package 1 Length	14.3 cm
Package 1 Weight	879.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	16.309 kg

Contractual warranty

Warranty	18 months
----------	-----------