

Product data sheet

Specifications



automatic insulation fault location
XD308C Vigilohm - 500...525 V AC
50/60 Hz

50726

ⓘ Discontinued

Main

Range	Vigilohm
Product Name	Vigilohm IFL
Device Short Name	XD308C
Number Of Channels	8
Mounting Position	Vertical

Complementary

Signalling Function	Insulation fault
Polling Time	20 s per connected channel
Test Function	Local
[Us] Rated Supply Voltage	500/525 V AC 50/60 Hz tolerance: - 15...10 %
Power Consumption In Va	6 VA
Mounting Mode	Flush-mounted
Mounting Support	Front face
Height	129 mm
Width	76 mm
Depth	115.5 mm
Net Weight	0.6 kg
Auxiliary Connection Terminal	Tunnel type terminals 1.5 mm²

Environment

Dielectric Strength	2500 V
Ip Degree Of Protection	IP30
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-25...70 °C

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications