

Product data sheet

Specifications



Thorsman - TMK-YH1720 - external corner - white RAL9010

5401121

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Thorsman
Product Name	Thorsman TMK
Product Or Component Type	External corner
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 10

Complementary

Trunking Material	Plastic
Trunking Dimension	17 x 20 mm
Fixing Mode	Snap-fitted
Material	ABS (acrylonitrile butadiene-styrene)
Length	55 mm
Height	22.5 mm
Width	55 mm

Environment

Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.1 cm
Package 1 Width	5.4 cm
Package 1 Length	5.4 cm
Package 1 Weight	6.0 g
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	6.5 cm
Package 2 Width	15.5 cm
Package 2 Length	18.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	74.0 g
------------------	--------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations