

Product data sheet

Specifications



Thorsman - TEK-U123 - trunking base - 72 mm - white RAL 9010 - 2.5 m

5526019

Main

Range Of Product	Thorsman
Product Name	Thorsman TEK
Product Or Component Type	Installation trunking
Cabling Installation System	Trunking
Colour Tint	White (RAL 9010)
Quantity Per Set	10 m

Complementary

Compartment Partitioning	1 compartment
Trunking Dimension	123 x 72 mm
Trunking Material	Plastic
Front Opening Size	80 mm
Fixing Mode	By brackets By screws
Material	PVC (polyvinyl chloride)
Length	2500 mm
Height	123 mm
Width	72 mm

Environment

Quality Labels	CE
Standards	EN 50085-1:1997/A1 EN 50085-1:1998 KEMA 55A:1984 SS 424 10 02:1993
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.200 cm
Package 1 Width	12.300 cm
Package 1 Length	250.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	2.800 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	112
Package 2 Height	84.000 cm
Package 2 Width	120.000 cm
Package 2 Length	240.000 cm
Package 2 Weight	313.600 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations