

Product data sheet

Specifications



Thorsman - POL-M20 - pole - two-sided - free-standing - white

5863832

Main

Range	Thorsman
Product Name	Thorsman POL
Product Or Component Type	Pole
Type Of Pole	Two-sided
Device Presentation	Pre-wired
Provided Equipment	2000 mm flexible conduit
Colour Tint	White (NCS 0402-B91G)
Number Of Power Socket Outlets	16 x 16 A - side earth
Number Of Data Socket Outlets	2 x RJ45 Cat.6 UTP 2 x RJ45 blind
Quantity Per Set	Set of 1
Adjustment	Fixed: 0 mm
Cover Plate Colour Tint	White
Useful Cross Section	10942 mm²
Compartment Partitioning	1 compartment

Complementary

Pole/Post Surface Finish	Powder coated
Pole Fixing Mode	Free-standing
Front Opening Size	80 mm
Material	Aluminium
Length	117 mm
Height	2150 mm
Width	120 mm
Cover Type	2 closed cover cover 80 mm in aluminium coated

Environment

Standards	PrEN 50085-2-4 SS 424 10 32 : 1989
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP30

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	28.5 cm
Package 1 Length	203.0 cm
Package 1 Weight	12.02 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	94.5 cm
Package 2 Width	120.0 cm
Package 2 Length	256.0 cm
Package 2 Weight	273.46 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	No need of specific recycling operations
---------------------	--