

Product data sheet

Specifications



Wibe - 90° exterior bend 15-1000 - steel Zinkpox coated white

728053

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Main

Range	Wibe
Range Of Product	Wibe Cable Ladders
Device Short Name	15
Product Or Component Type	90° exterior bend

Complementary

Direction Change Type	Horizontal
Inner Radius	1404 mm
Type Of Side Profile	Closed profile
Type Of Rung	Perforated profile
Product Destination	Cable ladder 1000 mm width
Material With Surface Treatment	Steel, Zinkpox coated white
Corrosion Class	C5-I
Height	55 mm
Width	2533 mm
Depth	2533 mm
Net Weight	1280 kg / set of 100

Environment

Mounting Location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards
-------------------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	253.3 cm
Package 1 Length	253.3 cm
Package 1 Weight	12.8 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations