

# Product data sheet

Specifications



## Unika interlocked socket - 32 A - 3P + N + E - 480...500 V AC - IP65 - wall

83099

⚠ Discontinued on: Jun 30, 2022

⚠ Discontinued

### Main

Range	PratiKa
Product Or Component Type	Interlocked socket
Device Short Name	Unika socket
Plug, Socket Category	Low voltage
Poles Description	3P + N + E
Network Type	AC
Outlet Standard	Industrial

### Complementary

Mounting Mode	Wall-mounted
[In] Rated Current	32 A
[Ue] Rated Operational Voltage	480...500 V
Network Frequency	50/60 Hz
Ground Lug Clockwise Position	7 h
Protection Type	Without protection
Plug, Socket Material	Housing: self-extinguishing engineering polymer
Contacts Material	Sleeves: nickel plated brass
Connections - Terminals	Captive screws
Maximum Cable Cross Section	10 mm²
Maximum Cable Outer Diameter	25 mm
Cable Entry	Cable gland
Thread Type	Pg 21
Net Weight	1.209 kg
Base Dimension	103 x 255 mm
Height	255 mm
Width	103 mm
Depth	153 mm
Colour	Grey (RAL 7035)
Voltage Colour	Black

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 60309-2 IEC 60309-1
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK09 conforming to EN 62262
Fire Resistance	750 °C conforming to IEC 60695-2-11
Relative Humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient Air Temperature For Operation	35 °C ( 86400 s ) -25...40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

## Contractual warranty

Warranty	18 months
----------	-----------