

Product data sheet

Specifications



250V 20A Philippines 3 Pin Socket 2M Sized Module, Bronze

84426MPH20_BZ

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E Philippines
Load Type	Inductive
Cover Plate Colour Tint	Bronze

Complementary

Device Mounting	Surface Flush
Rated Current	20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate base Polycarbonate cover
Connections - Terminals	Screw terminals
Width	45.8 mm
Height	46.7 mm
Depth	39 mm

Environment

Ambient Air Temperature For Storage	-5...60 °C
Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	10...95 %, non-condensing (operating) 10...95 %, non-condensing (storage)
Environmental Characteristic	UV resistant indoor use
Operating Altitude	2000 m
Standards	IEC 60884-1 BS 7671
Ip Degree Of Protection	IP20
Standards	BS 7671 IEC 60884-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	3.829 cm
Package 1 Width	4.67 cm
Package 1 Length	4.58 cm
Package 1 Weight	48 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	7.5 cm
Package 2 Width	10 cm
Package 2 Length	15.5 cm
Package 2 Weight	618.7 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	120
Package 3 Height	16.5 cm
Package 3 Width	21 cm
Package 3 Length	40 cm
Package 3 Weight	6106 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information