

Product data sheet

Specifications



selector switch Ø 30 - 2 positions - maintained - LED

9001K11J35LYFY

ⓘ Discontinued

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Illuminated selector switch
Device Short Name	9001K
Type Of Operator	maintained
Operator Profile	Yellow gloved hand knob

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	30 mm
Net Weight	0.245 kg
Shape Of Signaling Unit Head	Round
Operator Position Information	2 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Direct
Light Source	LED
Bulb Base	BA 9s
Light Block Colour	Yellow
[Us] Rated Supply Voltage	24...28 V AC/DC
Device Presentation	Basic element

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Degree Of Protection	NEMA 1
	NEMA 12
	NEMA 13
	NEMA 2
	NEMA 3
	NEMA 3R
	NEMA 4
	NEMA 6
Standards	JIS C 4520
	EN/IEC 60947-5-4
	UL 508
	EN/IEC 60947-1
	EN/IEC 60947-5-1
	JIS C 852
	CSA C22.2 No 14
Product Certifications	UL 508
	NEMA
Vibration Resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn conforming to IEC 60068-2-27

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov