

Product data sheet

Specifications



Illuminated selector switch head,
Harmony 9001K, metal, standard
handle, red, 30mm, 2 positions, stay
put, LED red, 120V

9001K11J38LRR

! Discontinued

! Discontinued on: Mar 31, 2023

! End-of-service on: Apr 15, 2023

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for illuminated selector switch
Device Short Name	9001K
Type Of Operator	maintained
Operator Profile	Red standard knob

Complementary

Bezel Material	Metal
Mounting Diameter	30 mm
Net Weight	0.245 kg
Shape Of Signaling Unit Head	Round
Operator Position Information	2 positions
Contacts Type And Composition	Without contact block
Mechanical Durability	500000 cycles
Light Block Supply	Direct
Light Source	LED
Bulb Base	BA 9s
Light Block Colour	Red
[Us] Rated Supply Voltage	120 V AC/DC
Device Presentation	Basic element
Cap/Operator Or Lens Colour	Red
[Us] Rated Supply Voltage	120 V
Light Source Colour	Red
Operator Profile	Standard handle
Type Of Operator	Stay put
Size	30 mm
Light Source	LED
Cam Profile	5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 NEMA 6
Standards	JIS C 852 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60947-1 UL 508 JIS C 4520
Product Certifications	NEMA UL 508
Vibration Resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn conforming to IEC 60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.903 cm
Package 1 Width	5.08 cm
Package 1 Length	32.774 cm
Package 1 Weight	249.476 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov