

Product data sheet

Specifications



PUSH BUTTON 600VAC 10A 30MM T-K

9001K2L35LYH6

 **Discontinued on:** Oct 11, 2019

 **Discontinued**

Main

Range Of Product	Harmony 9001K
Product Or Component Type	Illuminated push-button
Device Short Name	K
Type Of Operator	spring return
Operator Profile	Yellow projecting
Operator Additional Information	Without guard

Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	30 mm
Light Source	LED
Bulb Base	BA 9s
Light Block Supply	Direct
[Us] Rated Supply Voltage	24...28 V AC/DC
Contacts Type And Composition	1 NC
Connections - Terminals	Screw clamp terminals
Operating Position	Any position
[Ie] Rated Operational Current	10 A, AC-15 10 A, DC-13
Contact Operation	Standard
Device Presentation	Complete product

Environment

Product Certifications	NEMA CSA LR 25490 class 3211 03 CE UL listed file E42259 CCN NKCR
Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications