

# Product data sheet

Specifications



Illuminated push-button head,  
Harmony 9001K, metal, projecting,  
without cap, 30mm, spring return,  
LED red, 120V

9001K2L38LR

❗ Discontinued

❗ Discontinued on: Mar 31, 2023

## Main

Range Of Product	Harmony 9001K
Product Or Component Type	Head for illuminated push-button
Device Short Name	9001K
Mounting Diameter	30 mm
Light Source	Red LED

## Complementary

Bezel Material	Metal
Shape Of Signaling Unit Head	Round
Type Of Operator	spring return
Operator Profile	projecting, unmarked
Bulb Base	BA 9s
Light Block Supply	Direct 120 V AC/DC
Contacts Type And Composition	Without contact block
Mechanical Durability	5000000 cycles
Operating Position	Any position
Net Weight	0.166 kg
Cap/Operator Or Lens Colour	Without cap
[Us] Rated Supply Voltage	120 V
Light Source Colour	Red
Type Of Operator	Spring return
Operator Profile	Projecting

## Environment

Standards	UL 508 JIS C 4520 JIS C 852 EN/IEC 60947-1 EN/IEC 60947-5-4 CSA C22.2 No 14 EN/IEC 60947-5-1
Product Certifications	UL 508 NEMA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Vibration Resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529
Nema Degree Of Protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.7 cm
Package 1 Width	5 cm
Package 1 Length	9.5 cm
Package 1 Weight	176 g

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>