

# Product data sheet

Specifications



## SELECTOR SWITCH 600VAC 10A 30MM T-K

9001KS12FBH28

 **Discontinued on:** Oct 11, 2019

 **Discontinued**

### Main

Range Of Product	Harmony 9001K
Product Or Component Type	Selector switch
Device Short Name	K
Type Of Operator	maintained
Operator Profile	Black gloved hand knob

### Complementary

Bezel Material	Chromium plated metal
Mounting Diameter	30 mm
Operator Position Information	2 positions
Contacts Type And Composition	1 NO + 2 NC
Connections - Terminals	Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to IEC 60947-1
Device Presentation	Complete product

### Environment

Nema Degree Of Protection	NEMA 1/2/3/3R/4/6/12/13
Product Certifications	UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03 CE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications