

# Product data sheet

Specifications

## UPS Communications Cable Simple Signalling



940-0020

### Overview

Lead time	Usually in Stock
-----------	------------------

### Main

Number of rack unit	0U
Cable length	1.83 m
Number of cables	1
Product compatibility	UPS

### Physical

Colour	Grey
Net weight	0.45 kg
Mounting mode	Not rack-mountable
Cable end 2	SUB-D 9 male simple signaling
Cable end 1	SUB-D 9 female simple signaling

### Output

Number of port	1
----------------	---

### Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0.00...15240.00 m
Ambient air temperature for operation	0...45 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1

---

Package 1 Height	22.9 cm
Package 1 Width	5.1 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.45 kg

---

## Offer Sustainability

---

EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

---

## Contractual warranty

---

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)