

Product data sheet

Specifications



UPS Communications Cable Smart Signalling

940-0024

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Cable length	2.00 m
--------------	--------

Number of cables	1
------------------	---

Product compatibility	UPS
-----------------------	-----

Physical

Colour	Black
--------	-------

Net weight	0.46 kg
------------	---------

Mounting location	Front
-------------------	-------

Mounting mode	Not rack-mountable
---------------	--------------------

Cable end 2	SUB-D 9 male smart signaling
-------------	------------------------------

Cable end 1	SUB-D 9 female smart signaling
-------------	--------------------------------

Output

Number of port	1
----------------	---

Environmental

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0.00...15240.00 m
------------------	-------------------

Ambient air temperature for operation	0...45 °C
---------------------------------------	-----------

Relative humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient air temperature for storage	-15...45 °C
-------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Height	22.9 cm
Package 1 Width	5.1 cm
Package 1 Length	10.2 cm
Package 1 Weight	0.46 kg

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Recommended replacement(s)