

# Product data sheet

Specifications



## Auxiliary contact, Acti9, iSD, 1OC, AC/DC

A9A26927

⚠ To be discontinued on: Jun 1, 2024

⚠ To be discontinued

### Main

Range Of Product	Acti9
Product Or Component Type	Fault contact
Device Short Name	iSD
Signal Contacts Composition	1 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC DC-12 1.5 A at 60 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC AC-12 3 A at 415 V, AC 50/60 Hz AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

### Complementary

[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	86 mm
Width	9 mm
Depth	73 mm
Net Weight	33 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) 2 cable(s) 2.5 mm <sup>2</sup> - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm <sup>2</sup> - flexible with ferrule Screw clamp terminal (bottom) 1 cable(s) 0.5...2.5 mm <sup>2</sup> - flexible Screw clamp terminal (bottom) 1 cable(s) 1...4 mm <sup>2</sup> - rigid
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

### Environment

Standards	EN/IEC 60947-5-1
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution Degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...85 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	2.000 cm
Package 1 Length	9.200 cm
Package 1 Weight	40.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.500 cm
Package 2 Weight	570.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.373 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>