

# Product data sheet

Specifications



## Reflex iC60N Ti24 63 A 4P curve B integrated control MCB

A9C61463

### Main

Device Application	Control Distribution
Range	Acti9
Product Name	Reflex iC60
Device Short Name	Reflex iC60N
Product Or Component Type	Integrated control circuit breaker
Poles Description	4P
Number Of Protected Poles	4
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	B

### Complementary

[In] Rated Current	63 A
Network Frequency	50/60 Hz
Breaking Capacity Code	N
Breaking Capacity	20 kA Icu at 220...240 V AC 50/60 Hz conforming to EN/IEC 60947-2 10 kA Icu at 380...415 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Ui] Rated Insulation Voltage	500 V AC
Contact Position Indicator	Yes
Control Type	Toggle Remote control by pulse Remote control by continuous command ON/OFF button
Control Signal Type	Impulse Maintained very low voltage Maintained
Local Signalling	Flashing LED: device ready Red LED: fault Flashing LED: device tripped Green LED: device ON Flashing LED: device overheat
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz 24 V AC 50/60 Hz 48 V AC 50/60 Hz 24 V DC 48 V DC
[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Mounting Mode	Fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Support	35 mm symmetrical DIN rail
9 Mm Pitches	13
Height	84 mm
Width	117 mm
Depth	77 mm
Colour	White
Mechanical Durability	50000 cycles
Electrical Durability	AC-1: 50000 cycles AC 50 Hz
Provision For Padlocking	Padlockable
Locking Options Description	Padlock in OFF position
Earth-Leakage Protection	Separate block
Product Compatibility	With PLC

## Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	3
Tropicalisation	2
Relative Humidity	93 % at 40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.2 cm
Package 1 Width	11.2 cm
Package 1 Length	16.8 cm
Package 1 Weight	893.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.707 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>