

Product data sheet

Specifications



Acti9 iL single indicator light - Yellow - 110-230 Vac

A9E18324

Main

Range Of Product	Acti9
Product Name	Acti9 iL
Product Or Component Type	Modular pilot lighth
Device Short Name	iL
[Us] Rated Supply Voltage	110...230 V AC at 50/60 Hz 110...130 V DC

Complementary

Indicator Light	1 LED yellow, service life 100000 h of constant lighting efficiency (consumption 0.3 W)
Mounting Mode	Fixed
Mounting Support	Symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	69.5 mm
Colour	White (RAL 9003)
Auxiliary Connection Terminal	Tunnel type terminal 1 cable(s) rigid 0.5 mm² Tunnel type terminal 2 cable(s) rigid 2.5 mm² Tunnel type terminal 1 cable(s) flexible 0.5 mm² Tunnel type terminal 2 cable(s) flexible 2.5 mm² Tunnel type terminal 2 cable(s) flexible with ferrule 2.5 mm²
Wire Stripping Length	9 mm
Tightening Torque	1 N.m

Environment

Standards	IEC 60947-5-1
Ip Degree Of Protection	IP2 IPxx B
Pollution Degree	3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-35...70 °C
Ambient Air Temperature For Storage	-40...80 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.600 cm
Package 1 Width	1.800 cm
Package 1 Length	8.200 cm
Package 1 Weight	39.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	7.800 cm
Package 2 Width	9.800 cm
Package 2 Length	23.300 cm
Package 2 Weight	523.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	5.159 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts & Cables
Product

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

No need of specific recycling operations