

Product data sheet

Specifications



iQuick PRD20r modular surge arrester - 3 poles - 350V - with remote transfer

A9L16296

Main

Range Of Product	Acti9
Product Name	Acti9 iQuick PRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iQuick PRD20r
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	NF KEMA-KEUR
Poles Description	3P
Remote Signalling	With
Signal Contacts Composition	1 SD (1 C/O)
Surge Arrester Type	Electrical distribution network
Earthing System	TN-C IT 230

Complementary

Surge Arrester Class Type	Type 2
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 5 kA (L/PE) Differential mode: 5 kA (L/N)
[Imax] Maximum Discharge Current	Common mode: 20 kA L/PE
[Uc] Maximum Continuous Operating Voltage	Common mode: 350 V L/PE
Maximum [Up] Voltage Protection Level	Common mode <1.5 kV type 2 L/PE
Disconnecter Device Type	Integrated circuit breaker - Icu 25 kA
Signalling Circuit Voltage	2 A/250 V AC 50/60 Hz
Mounting Mode	Clip-on (DIN rail)
9 Mm Pitches	12.7
Height	94 mm
Width	113.6 mm
Depth	75.9 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.67 kg
Colour	White (RAL 9003)
Connections - Terminals	Tunnel type terminal (downside) 2.5...25 mm² Tunnel type terminal (upside) 2.5...25 mm²
Tightening Torque	2.5 N.m

Environment

Ik Degree Of Protection	IK05 conforming to IEC 62262
Relative Humidity	5...95 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.0 cm
Package 1 Width	10.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	740.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.32 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts & Cables
Product

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

No need of specific recycling operations