

Product data sheet

Specifications



Voltage release MN 115Vac 400hzdc

A9N26959

Main

Range Of Product	Acti9
Product Or Component Type	Undervoltage release
Device Short Name	MN
[Uc] Control Circuit Voltage	115 V AC 400 Hz
Control Type	Standard
9 Mm Pitches	2

Complementary

Range Compatibility	Acti 9 Acti9 iDPN Acti 9 Acti9 C120 Acti 9 Acti9 C40 Acti 9 Acti9 C60H-DC Acti 9 Acti9 C60NA-DC Acti 9 Acti9 C60PV-DC Acti 9 Acti9 DPN Vigi Acti 9 Acti9 DT40 Acti 9 Acti9 DT60 Acti 9 Acti9 ID C40 Acti 9 Acti9 IDc Acti 9 Acti9 ITG40 Acti 9 Acti9 ID Acti 9 Acti9 DPN
Local Signalling	Action indicator
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	82.5 mm
Width	18 mm
Depth	73.5 mm
Net Weight	66 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm² - flexible Screw clamp terminal (bottom) - 2 cable(s) 1.5 mm² - flexible with ferrule Screw clamp terminal (bottom) - 1 cable(s) 0.5...2.5 mm² - rigid
Wire Stripping Length	9 mm for bottom connection
Tightening Torque	1 N.m bottom

Environment

Standards	EN/IEC 60947-5-1
-----------	------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	KEMA LCIE ASEFA ASTA
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-25...50 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	9.4 cm
Package 1 Length	8 cm
Package 1 Weight	84 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8.5 cm
Package 2 Width	9.8 cm
Package 2 Length	26.5 cm
Package 2 Weight	678 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	6.31 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information