

Product data sheet

Specifications



switch Acti9 iSW - 2 poles - 63A - 415V

A9S60263

⚠ Discontinued on: Dec 15, 2020

⚠ Discontinued

Main

Range	Acti9
Product Name	Acti9 iSW
Product Or Component Type	Switch disconnecter
Device Short Name	iSW
Device Application	Control Isolation
Poles Description	2P
Utilisation Category	AC-22A conforming to EN 60947-3 AC-22A conforming to IEC 60947-3
Suitability For Isolation	Yes conforming to EN 60947-3 Yes conforming to IEC 60947-3

Complementary

[Ie] Rated Operational Current	63 A at 415 V AC 50/60 Hz
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN 60947-3 6 kV conforming to IEC 60947-3
Control Type	Toggle
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Standard
9 Mm Pitches	4
Height	77 mm
Width	36 mm
Depth	70 mm
Colour	White
Mechanical Durability	50000 cycles
Electrical Durability	20000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Tunnel type terminals - <= 50 mm² - rigid Tunnel type terminals - <= 35 mm² - flexible Tunnel type terminals - <= 35 mm² - flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	3.5 N.m

Environment

Standards	IEC 60947-3
Ip Degree Of Protection	IP4
Pollution Degree	3 conforming to IEC 60947-3
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-20...50 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	3.5 cm
Package 1 Length	8 cm
Package 1 Weight	0.149 kg

Contractual warranty

Warranty	18 months
----------	-----------